

US010281600B2

# (12) United States Patent

# **Degtiarenko**

## (54) NEUTRON DETECTOR AND DOSE RATE METER USING BERYLLIUM-LOADED MATERIALS

(71) Applicant: JEFFERSON SCIENCE

ASSOCIATES, LLC, Newport News,

VA (US)

(72) Inventor: Pavel V. Degtiarenko, Williamsburg,

VA (US)

(73) Assignee: **JEFFERSON SCIENCE** 

ASSOCIATES, LLC, Newport News,

VA (US)

(\*) Notice: Subject to any disclaimer, the term of this

patent is extended or adjusted under 35

U.S.C. 154(b) by 0 days.

(21) Appl. No.: 15/950,298

(22) Filed: Apr. 11, 2018

(65) **Prior Publication Data** 

US 2018/0299570 A1 Oct. 18, 2018

#### Related U.S. Application Data

- (60) Provisional application No. 62/485,098, filed on Apr. 13, 2017.
- (51) Int. Cl. G01T 7/00 (2006.01) G01T 3/06 (2006.01) G01T 3/00 (2006.01)
- (52) **U.S. CI.**CPC ....... *G01T 7/00* (2013.01); *G01T 3/00* (2013.01); *G01T 3/06* (2013.01); *G01T 3/06*

(10) Patent No.: US 10,281,600 B2

(45) **Date of Patent:** 

May 7, 2019

(58) Field of Classification Search

CPC .. G01T 3/00; G01T 3/06; G01T 3/008; G01T

See application file for complete search history.

(56) References Cited

U.S. PATENT DOCUMENTS

2017/0003400 A1\* 1/2017 Carasco ....... G01T 3/00

#### OTHER PUBLICATIONS

I. O. Andersson, "Neutron rem-counter with uniform sensitivity from 0.025 eV to 10 MeV", in: Proceedings of the IAEA Symposium on neutron dosimetry, Vienna, 2:87-95, 1963.

C. Birattari et al., "An Extended Range Neutron Rem Counter", Nuclear Instruments and Methods in Physics Research A297:250-257, Elsevier Science Publishers, Holland, 1990.

R. H. Olsher, et al., "WENDI: An Improved Neutron REM Meter", Health Physics, 79(2):170ff, 2000, p. 170-181, Los Alamos, NM.


(Continued)

Primary Examiner — David P Porta

#### (57) ABSTRACT

An apparatus and method for improving the sensitivity and energy response of neutron detectors and neutron dose rate meters. A beryllium layer is added to neutron detector moderators to improve the sensitivity of the detector. Energy dependence of the sensitivity is optimized by controlling the amount of beryllium in the moderator and by specifying the geometrical design parameters. The beryllium layer, in combination with additional material layers in the moderator, makes the detector response function correspond to the theoretical one in a wide range of energies. Response parameters of the neutron dose rate meter are within 20% of the theoretical response function in the neutron energy range from 500 keV to 10 GeV, and also in the energy range corresponding to thermal neutrons (about 1-100 meV).

## 19 Claims, 6 Drawing Sheets



(2013.01)